

Coating Overview

Characterization of the produced PVD/PACVD Coatings



LET'S OPTIMIZE EXCELLENCE

H-O-T Coating Name	Coating Material	Coating Structure	Coating Hardness (HV)	Coating Thickness (µm)*	Max. Service Temperature (° C)	Coefficient of Friction (dry) vs. steel	Coating Colour
TiN	TiN	monolayered	2200 – 2600	3	600	0,4	gold
TiCN	TiCN	multilayered	2600 – 3200	3	400	0,3	blue-grey
NovaDur® HD	AlTiSiN	nanocomposite	3400 – 3700	3	900	0,4	black-grey
NovaDur® Prime	AlCrN	nanostructured	3200 – 3500	till 3	1100	0,4	anthracite
NovaDur® Prime evo	AlCrTiN	nanostructured	3200 – 3500	till 5	1100	0,4	anthracite
NovaDur® Uni	AlTiN	nanostructured	3000 – 3200	3	900	0,4	black-grey
NovaDur® TH	AlTiSiN	nanocomposite	3000 – 3200	3	1100	0,4	old gold
NovaDur® F evo	AlCrTiN	nanostructured	3000 – 3400	till 10	1100	0,4	black-grey
NovaDur® HC	AlTiSiN	nanocomposite	3000 – 3400	3	1100	0,4	copper
Calida® HP	AlTiN	nanostructured	3200 – 3800	3	1100	0,4	old rose
Calida® PD	AlTiN	nanostructured	3000 – 3400	3	900	0,4	copper
Calida® Z	ZrCrN	multilayered	2300 – 2600	3	600	0,4	light yellow gold
Calida® Cr	CrN-Cr	multilayered	1900 – 2400	till 8	800	0,4	silver-grey
CrN	CrN	monolayered	1500 – 1900	till 5	600	0,4	silver-grey
TT®-Cr₂N	Cr ₂ N	monolayered	1800 – 2500	2	700	0,4	silver-grey
TT®-WCC®	W-C:H	lamellar	1100 – 1500	3	350	0,2	black-grey
TT®-DLC	a-C:H	multilayered	2000 – 3500	3	350	< 0,15	black-grey
TT®-C-DLC	a-C:H	multilayered	2500 – 3100	2	350	0,12	black-grey
TT®-ta-C	ta-C	monolayered	4500 – 7000	till 1.5	450	0,07	rainbow to black-grey

* Coating thickness depending on application (with coating thickness tolerance +/- 1 µm)

Application recommendations

	Drilling	Turning	Milling	Tapping	Reaming	Broaching	Hobbing	Slotting	Punching/ Precision Blanking	Forming
Unalloyed Steel	<i>NovaDur®HD</i> <i>Calida®PD</i>	<i>NovaDur® Prime</i> <i>NovaDur®TH</i> <i>Calida®HP</i>	<i>NovaDur® Prime</i> <i>NovaDur®Uni</i> <i>NovaDur®TH</i> <i>Calida®HP</i>	TiN <i>NovaDur® Prime</i>	TiN	TiCN <i>NovaDur®Uni</i>	<i>NovaDur® Prime evo</i> <i>NovaDur®Uni</i>	<i>NovaDur® Prime evo</i> <i>NovaDur®Uni</i>	TiCN <i>NovaDur® Prime</i>	TiCN <i>NovaDur®F evo</i>
Alloyed Steel	<i>NovaDur®HD</i> <i>Calida®PD</i>	<i>NovaDur® Prime</i> <i>NovaDur®TH</i> <i>Calida®HP</i>	<i>NovaDur® Prime</i> <i>NovaDur®Uni</i> <i>NovaDur®TH</i> <i>Calida®HP</i>	TiN <i>NovaDur® Prime</i>	TiN	TiCN <i>NovaDur®Uni</i>	<i>NovaDur® Prime evo</i> <i>NovaDur®Uni</i>	<i>NovaDur® Prime evo</i> <i>NovaDur®Uni</i>	TiCN <i>NovaDur®F evo</i> <i>NovaDur®TH</i>	TiCN <i>NovaDur®F evo</i>
High-Alloyed Steel	<i>NovaDur®HD</i> <i>Calida®PD</i>	<i>NovaDur® Prime</i> <i>NovaDur®TH</i> <i>Calida®HP</i>	<i>NovaDur® Prime</i> <i>NovaDur®Uni</i> <i>NovaDur®TH</i> <i>Calida®HP</i>	<i>NovaDur® Prime</i> <i>NovaDur®Uni</i> <i>Calida®HP</i>	<i>NovaDur®Uni</i> <i>Calida®HP</i>	TiCN <i>NovaDur®Uni</i>	<i>NovaDur® Prime evo</i> <i>NovaDur®Uni</i>	<i>NovaDur® Prime evo</i> <i>NovaDur®Uni</i>	TiCN <i>NovaDur®F evo</i> <i>NovaDur®TH</i>	TiCN <i>NovaDur®F evo</i>
Pre-Hardened Steel	<i>NovaDur®HD</i> <i>Calida®PD</i>	<i>NovaDur® Prime</i> <i>NovaDur®TH</i> <i>Calida®HP</i>	<i>NovaDur® Prime</i> <i>NovaDur®Uni</i> <i>NovaDur®TH</i> <i>Calida®HP</i>	<i>NovaDur® Prime</i> <i>NovaDur®Uni</i> <i>Calida®HP</i>	<i>NovaDur®Uni</i> <i>Calida®HP</i>	TiCN <i>NovaDur®Uni</i>	<i>NovaDur® Prime evo</i> <i>NovaDur®Uni</i>	<i>NovaDur® Prime evo</i> <i>NovaDur®Uni</i>	TiCN <i>NovaDur®F evo</i>	TiCN <i>NovaDur®F evo</i>
Hardened Steel ≤ 54 HRC	<i>NovaDur®HD</i> <i>Calida®PD</i>	<i>NovaDur® Prime</i> <i>NovaDur®TH</i>	<i>NovaDur® Prime</i> <i>NovaDur®Uni</i>	<i>NovaDur® Prime</i> <i>NovaDur®Uni</i> <i>NovaDur®TH</i>	<i>NovaDur®Uni</i> <i>Calida®HP</i>	–	–	–	–	–
Hardened Steel > 54 HRC	<i>NovaDur®HD</i> <i>Calida®PD</i>	<i>NovaDur®TH</i> <i>Calida®HP</i>	<i>NovaDur®TH</i> <i>Calida®HP</i>	–	<i>NovaDur®Uni</i> <i>Calida®HP</i>	–	–	–	–	–
Stainless Steel	<i>NovaDur® Prime</i> <i>NovaDur®HC</i>	<i>NovaDur® Prime</i> <i>NovaDur®HC</i>	<i>NovaDur® Prime</i> <i>NovaDur®HC</i>	<i>NovaDur® Prime</i> <i>NovaDur®HC</i>	<i>NovaDur®HC</i>	–	–	–	<i>NovaDur®HC</i>	TiCN <i>NovaDur®F evo</i>
Cast Iron	<i>NovaDur® Prime</i> <i>NovaDur®HD</i>	<i>NovaDur® Prime</i> <i>NovaDur®HD</i>	<i>NovaDur® Prime</i> <i>NovaDur®HD</i>	<i>NovaDur® Prime</i> <i>NovaDur®HD</i>	<i>NovaDur® Prime</i>	–	<i>NovaDur® Prime evo</i> <i>NovaDur®Uni</i>	<i>NovaDur® Prime evo</i> <i>NovaDur®Uni</i>	–	–
Copper	<i>Calida®Z</i> <i>TT®-ta-C</i> (rainbow 0,5 µm)	<i>Calida®Z</i> <i>TT®-ta-C</i>	<i>Calida®Z</i> <i>TT®-ta-C</i> (rainbow 0,5 µm)	<i>Calida®Z</i> <i>TT®-ta-C</i>	CrN <i>TT®-ta-C</i>	–	–	–	CrN <i>TT®-ta-C</i>	<i>TT®-ta-C</i> (black-grey 1,5 µm)
Brass/Nickel Silver	<i>Calida®Z</i> <i>TT®-ta-C</i> (rainbow 0,5 µm)	<i>Calida®Z</i> <i>TT®-ta-C</i>	<i>Calida®Z</i> <i>TT®-ta-C</i> (rainbow 0,5 µm)	<i>Calida®Z</i> <i>TT®-ta-C</i>	CrN <i>TT®-ta-C</i>	–	–	–	CrN <i>TT®-ta-C</i>	<i>TT®-ta-C</i> (black-grey 1,5 µm)
Plastics	<i>Calida®Z</i> <i>TT®-C-DLC</i>	<i>Calida®Z</i> <i>TT®-C-DLC</i>	<i>Calida®Z</i> <i>TT®-C-DLC</i>	–	<i>TT®-ta-C</i> <i>TT®-C-DLC</i>	–	–	–	–	<i>TT®-ta-C</i> (black-grey 1,5 µm)
Al Alloys	<i>Calida®Z</i> <i>TT®-C-DLC</i> <i>TT®-ta-C</i>	<i>Calida®Z</i> <i>TT®-C-DLC</i> <i>TT®-ta-C</i>	<i>Calida®Z</i> <i>TT®-C-DLC</i> <i>TT®-ta-C</i>	<i>Calida®Z</i> <i>TT®-C-DLC</i> <i>TT®-ta-C</i>	<i>Calida®Z</i> <i>TT®-C-DLC</i> <i>TT®-ta-C</i>	–	–	–	<i>Calida®Z</i> <i>TT®-ta-C</i>	<i>Calida®Z</i> <i>TT®-ta-C</i> (black-grey 1,5 µm)
Ti Alloys	<i>NovaDur®HC</i> <i>TT®-ta-C</i>	<i>NovaDur® HC</i> <i>TT®-ta-C</i>	<i>NovaDur® HC</i> <i>TT®-ta-C</i>	<i>NovaDur® HC</i> <i>TT®-ta-C</i>	<i>NovaDur® HC</i> <i>TT®-ta-C</i>	–	–	–	<i>NovaDur®F evo</i>	<i>NovaDur®F evo</i>
Inconel	<i>NovaDur®TH</i>	<i>NovaDur®TH</i>	<i>NovaDur®TH</i>	<i>NovaDur®TH</i>	<i>NovaDur®TH</i>	–	–	–	–	–
Wood materials	<i>TT®-ta-C</i>	<i>TT®-ta-C</i>	<i>TT®-ta-C</i>	<i>TT®-ta-C</i>	<i>TT®-ta-C</i>	–	–	–	–	–
Composite Materials (GFC/CFC)	<i>TT®-ta-C</i>	<i>TT®-ta-C</i>	<i>TT®-ta-C</i>	<i>TT®-ta-C</i>	<i>TT®-ta-C</i>	–	–	–	–	–